




ISOMETRIC VIEW



ALLIANCE SENSORS INDUCTIVE LINEAR POSITION SENSOR, SLIDE, 150MM STROKE, 12.5MM SHAFT DIAMETER, 4-20 MA OUTPUT, 45MM DIAMETER X 301.7MM BODY, ROD EYES MOUNT, 5-PIN M12 QUICK-DISCONNECT.

LVI45-150R-01-20S

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
3/22/2022

SHEET 1 OF 1