




EXTENDED VIEW



RETRACTED VIEW



ISOMETRIC VIEW



ALLIANCE SENSORS INDUCTIVE LINEAR POSITION SENSOR, SLIDE, 12.7MM STROKE, 5.2MM SHAFT DIAMETER, 0-10 VDC OUTPUT, 19MM DIAMETER X 35MM BODY, M5 X 0.8 MOUNT, PIGTAIL, 3.2FT/1M CABLE LENGTH.

**LZE19-12.7A-00-10S**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
[mm]

LATEST VERSION  
3/22/2022

SHEET 1 OF 1