



CUTOUT TEMPLATE VIEWED FROM INSIDE ENCLOSURE. FLIP IF APPLIED TO OUTSIDE OF ENCLOSURE.

TE40-050-17-4X	
Units:	inches [mm]
Scale:	Full
ENCLOSURE HEAT EXCHANGER, 4887 BTU/H, 120VAC, SIDE MOUNT, 304 SS FOR UL TYPE 4X ENCLOSURE	
AUTOMATIONDIRECT	