



CUTOUT TEMPLATE VIEWED FROM INSIDE ENCLOSURE. FLIP IF APPLIED TO OUTSIDE OF ENCLOSURE.

TE40-050-24D-04	
Units:	inches [mm]
Scale:	Full
ENCLOSURE HEAT EXCHANGER, 4887 BTU/H, 24VDC, SIDE MOUNT, ANSI 61 FOR UL TYPE 4 ENCLOSURE	
AUTOMATIONDIRECT	