



TABLE A

PART NO	LENGTH(1)
USB-CBL-AB1	.3m (1 ft.)
USB-CBL-AB3	.9m (3 ft.)
USB-CBL-AB6	1.8m (6 ft.)
USB-CBL-AB10	3.0m (10 ft.)
USB-CBL-AB15	4.57m (15 ft)



## PIN-OUT DIAGRAM



## NOTES:

1. (USB2.0) UL2725 28AWG\*1PAIR+24AWG\*2C  
+AEB, OD: 4.5mm, JACKET GOLD TRANSPARENT COLOR
2. USB A TYPE MALE SOLDERING TYPE.  
INSULATION: PBT, WHITE COLOR.  
CONTACT: BRASS, GOLD-PLATED(30u").  
SHELL GOLD-PLATED
3. USB B TYPE MALE SOLDERING TYPE.  
INSULATION: PBT, WHITE COLOR.  
CONTACT: BRASS, GOLD-PLATED(30u").  
SHELL GOLD-PLATED
4. MINIMUM BEND RADIUS: 27MM

USB-CBL-ABn	
Rev: original	Date: 06/2009
Units: mm [inches]	
Scale: none	
ZIPLINK USB A/B Cable	