





WIRING	
COLOR	FUNCTION
J1 - +	V+ (ALL PORTS PIN 1)
J1 - -	V- (ALL PORTS PIN 3)
J1-GND	GND (ALL PORTS PIN 5)
J1 - 1	PORT 1 PIN 4
J1 - 2	PORT 2 PIN 4
J1 - 3	PORT 3 PIN 4
J1 - 4	PORT 4 PIN 4
J1 - 5	PORT 5 PIN 4
J1 - 6	PORT 6 PIN 4
J2 - 1	PORT 1 PIN 2
J2 - 2	PORT 2 PIN 2
J2 - 3	PORT 3 PIN 2
J2 - 4	PORT 4 PIN 2
J2 - 5	PORT 5 PIN 2
J2 - 6	PORT 6 PIN 2
VOLTS	48 VDC MAX
AMPS	3A PER PORT, 8A PER BLOCK



CONNECTIONS MADE VIA SPRING CLAMP TERMINAL BLOCKS




THIS IS A LIGHTED PNP BLOCK

MATERIALS	
BODY	PBT
MARKERS	POLYAMIDE
INSERTS	POLYAMIDE
GLAND	POLYAMIDE
CONTACTS	GOLD PLATED COPPER ALLOY
O-RINGS	NBR

ZP-JBH65-2P-FW

Units: inches [mm]
Scale: 1:1
ZIP-Port Junction Block


AUTOMATIONDIRECT
.com