



Some versions of SV2C-PC12-xxxx are manufactured with fork terminals. If used with a SV2A-2150 drive, remove the U,V,W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended.

| CABLES | | |
|---|---|---|
| CABLE PART # | LENGTH L (IN) | LENGTH L (mm) |
| SV2C-PC12-03FB | 118 | 3000 |
| SV2C-PC12-05FB | 197 | 5000 |
| SV2C-PC12-10FB | 394 | 10000 |
| SV2C-PC12-20FB | 787 | 20000 |

# SV2C-PC12-03FB

Units: mm [inch]

Full Scale

SureServo2 POWER FLEX CABLE, MATING CONNECTIONS, 9.8FT/3m CABLE LENGTH, FOR USE WITH 1 kW MEDIUM INERTIA AND 1.5 kW SureServo2 MOTORS WITH BRAKE

AUTOMATIONDIRECT.com

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.