


Some versions of SV2C-PC12-xxxx are manufactured with fork terminals. If used with a SV2A-2150 drive, remove the U,V,W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended.

CABLES		
CABLE PART #	LENGTH L (IN)	LENGTH L (mm)
SV2C-PC12-03FB	118	3000
SV2C-PC12-05FB	197	5000
SV2C-PC12-10FB	394	10000
SV2C-PC12-20FB	787	20000

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

SV2C-PC12-20FB

Units: mm [inch]

Full Scale

SureServo2 POWER FLEX CABLE, MATING CONNECTIONS, 65.6FT/20m CABLE LENGTH, FOR USE WITH 1 kW MEDIUM INERTIA AND 1.5 kW SureServo2 MOTORS WITH BRAKE

AUTOMATIONDIRECT.com