

TABLE A

PART NO.	LENGTH
ZL-HD15M-CBL-2P	2.0m (6.6ft)



PIN-OUT DIAGRAM



NOTES:
1. CABLE: UL2464 8P#26+AEB, LENGTH 2M, 0D: 8MM BLACK
2. CURRENT: 0.25A, 3.75A MAX CABLE CURRENT
3. VOLTAGE
   - 24V AC/DC RATED OPERATING VOLTAGE
   - 30V AC/DC MAXIMUM VOLTAGE
4. OPERATING TEMPERATURE: 0-60°C (32-140°F)
5. P1 CONNECTOR: HDB 15P MALE SOLDERING TYPE.
6. P2 CONNECTOR: 15 TINNED PIG-TAIL LEADS
7. MINIMUM BEND RADIUS: 65.6MM [2.58IN]
8. THUMBSCREW: #4-40*30.5

ZL-HD15M-CBL-2P	
Rev: A2	Date: 8/26/2019
Units: mm [inches]	
Scale: 1:1	

ZIPLink
Connector Module Cable

AUTOMATIONDIRECT.com