

TABLE A

PART NO.	LENGTH
ZL-HD15M-CBL-DB15F	2m (6.5ft)





Notes:
1. Cable: UL2464 8P#26+AEB, LENGTH 2M, OD: 8MM BLACK
2. P1: HD15P Male Soldering Type.
   Insulation Type: PBT Black Color
   Contact: Brass, Gold Flash
3. P2: DB15P Female Soldering Type.
   Insulation Type: PBT Black Color
   Contact: Brass, Gold Flash
4. Thumb Screw: #4/40*30.5
5. Minimum Bend Radius: 65.6mm [2.58"]
6. Operating Temperature: 0-60°C (32-140°F)

ZL-HD15M-CBL-DB15F	
Rev: A2	Date: 8/26/2019
Units: mm [inches]	
Scale: none	
ZIPLINK Comm Cable	
AUTOMATIONDIRECT	