


011640-00
Units: inches [mm]
Scale: Full
DUAL THERMOSTAT, FIXED POINT
NO 50°C CLOSED / 40°C OPEN,
NO 60°C CLOSE / 50°C OPEN
 AUTOMATIONDIRECT .com