





TOP VIEW

SECTION B-B
SIDE VIEW




SECTION A-A
SIDE VIEW



INSIDE BOX

INSIDE LID



POLYCARBONATE
VERSION ONLY
c  US LISTED
FILE #E65324
TYPE 4,4X,6,6P

Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change.
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 4 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

1554JL		
1554JL Regular Enclosure		
General Purpose ABS RAL-7035		1554JLGY
Polycarbonate RAL-7035		1554JL2GY
1554JL Clear / Smoke Lid Enclosure		
Polycarbonate Box / Clear Polycarbonate Lid		1554JL2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid		1554JL2GYSL
ACCESSORIES		
Steel Inner Panels		1554JPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)		1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)		1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)		SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)		1554JGASKET



HAMMOND

MANUFACTURING®

1554JL2GY

www.hammondmfg.com

Dimensions:
mm
[inches]