





TOP VIEW

SECTION B-B
SIDE VIEW




SECTION A-A
SIDE VIEW



INSIDE BOX

INSIDE LID



POLYCARBONATE
VERSION ONLY
UL US LISTED
FILE #E65324
TYPE 4,4X,6,6P

Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change.
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 4 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

| 1554JL | | |
|---|--|-------------|
| 1554JL Regular Enclosure | | |
| General Purpose ABS RAL-7035 | | 1554JLGY |
| Polycarbonate RAL-7035 | | 1554JL2GY |
| 1554JL Clear / Smoke Lid Enclosure | | |
| Polycarbonate Box / Clear Polycarbonate Lid | | 1554JL2GYCL |
| Polycarbonate Box / Smoke Polycarbonate Lid | | 1554JL2GYSL |
| ACCESSORIES | | |
| Steel Inner Panels | | 1554JPL |
| Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100) | | 1591MM100 |
| Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100) | | 1598ATS100 |
| Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50) | | SC576-50 |
| Silicone Pre-formed Gasket Black (Pkg 2) | | 1554JGASKET |



HAMMOND

MANUFACTURING®

1554JL2GYCL

www.hammondmfg.com

Dimensions:
mm
[inches]