




TOP VIEW


SECTION B-B  
SIDE VIEW




SECTION A-A  
SIDE VIEW



INSIDE BOX



INSIDE LID



POLYCARBONATE  
VERSION ONLY  
UL US LISTED  
FILE #E65324  
TYPE 4,4X,6,6P

Solid models of this enclosure available in .stp or .x\_t  
(Part number and text placement/orientation on our products are subject to change.  
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 4 cover screws, and preformed silicone gasket.  
General Purpose ABS version is not UL approved. (Matl UL94 - HB)  
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

1554JL		
1554JL Regular Enclosure		
General Purpose ABS RAL-7035		1554JLGY
Polycarbonate RAL-7035		1554JL2GY
1554JL Clear / Smoke Lid Enclosure		
Polycarbonate Box / Clear Polycarbonate Lid		1554JL2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid		1554JL2GYSL
ACCESSORIES		
Steel Inner Panels		1554JPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)		1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)		1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)		SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)		1554JGASKET



MANUFACTURING®

1554JLGY

www.hammondmfg.com