




TOP VIEW





SECTION A-A
SIDE VIEW




INSIDE BOX



SECTION B-B
SIDE VIEW



INSIDE LID



POLYCARBONATE
VERSION ONLY

UL US LISTED

FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 4 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

1554LA

1554LA Regular Enclosure

General Purpose ABS RAL-7035	1554LAGY
------------------------------	----------

Polycarbonate RAL-7035	1554LA2GY
------------------------	-----------

1554LA Clear / Smoke Lid Enclosure

Polycarbonate Box / Clear Polycarbonate Lid	1554LA2GYCL
---	-------------

Polycarbonate Box / Smoke Polycarbonate Lid	1554LA2GYSL
---	-------------

ACCESSORIES

Steel Inner Panels	1554LPL
--------------------	---------

Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
---	-----------

Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
---	------------

Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
--	----------

Silicone Pre-formed Gasket Black (Pkg 2)	1554LGASKET
--	-------------



Dimensions:
mm
[inches]