




**TOP VIEW**




**SECTION A-A  
SIDE VIEW**




**INSIDE BOX**




**SECTION B-B  
SIDE VIEW**



**STEEL PANEL  
ORDER SEPARATELY**



**INSIDE LID**



POLYCARBONATE  
VERSION ONLY



Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)  
Contact Factory (modshop@hammfg.com) for quotes  
Solid models of this enclosure available in .stp or .x\_t  
(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)

**NOTE**

Purchased assembly includes box, lid, 4 cover screws, and preformed silicone gasket.  
General Purpose ABS version is not UL approved. (Matl UL94 - HB)  
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

**Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)**

**1554QA**

**1554QA Regular Enclosure**


General Purpose ABS RAL-7035	1554QAGY
Polycarbonate RAL-7035	1554QA2GY

**1554QA Clear / Smoke Lid Enclosure**

Polycarbonate Box / Clear Polycarbonate Lid	1554QA2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid	1554QA2GYSL

**ACCESSORIES**

Steel Inner Panels	1554QPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554QGASKET



**Dimensions:**  
mm  
[inches]