





POLYCARBONATE  
VERSION ONLY  
**UL** US LISTED  
FILE #E65324  
TYPE 4,4X,6,6P



SECTION A-A  
(INSIDE LENGTH)  
SIDE VIEW



INSIDE BOX

INSIDE LID

**Solid models of this enclosure available in .stp or .x\_t**  
(Part number and text placement/orientation on our products are subject to change.  
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 6 cover screws, and preformed silicone gasket.

General Purpose ABS version is not UL approved. (Mail UL94 - HB)

Polycarbonate version is UL 508A approved. (Mail UL94 - 5VA @ 3mm)

**Recommended Cover screw torque -- 71-85 ozf-in (50-60 cN-m)**

1554VAL	
1554VAL Regular Enclosure	
General Purpose ABS RAL-7035	1554VALGY
Polycarbonate RAL-7035	1554VAL2GY
1554VAL Clear / Smoke Lid Enclosure	
Polycarbonate Box / Clear Polycarbonate Lid	1554VAL2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid	1554VAL2GYSL
ACCESSORIES	
Steel Inner Panels	1554VAPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated] (Pkg 100)	1598ATS100
Stainless Steel Cover Screws [M4-0.7 X 25mm] (Pkg 50)	SC583-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554VAGASKET



MANUFACTURING®

1554VAL2GY

www.hammondmfg.com

Dimensions:  
mm  
[inches]