POLYCARBONATE  
VERSION ONLY






FILE #E65324  
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)

Contact Factory (modshop@hammfg.com) for quotes

Solid models of this enclosure available in .stp or .x\_t

(Part number and text placement/orientation on our products are subject to change, we do not recommend using them as a locating reference for modification purposes)



## INSIDE LID

**Dimensions:**  
mm  
[inches]

<b>NOTE</b>	
<p>Purchased assembly includes box, lid, 6 cover screws, and preformed silicone gasket.</p> <p>General Purpose ABS version is not UL approved. (Matl UL94 - HB)</p> <p>Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)</p>	
<b>Recommended Cover screw torque -- 8-9 lbf-in (90-100 cN-m)</b>	

1554X	
1554X Regular Enclosure	
General Purpose ABS RAL-7035	1554XGY
Polycarbonate RAL-7035	1554X2GY
1554X Clear / Smoke Lid Enclosure	
Polycarbonate Box / Clear Polycarbonate Lid	1554X2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid	1554X2GYSL
ACCESSORIES	
Steel Inner Panels	1554XPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#8 X 5/16" (6.4mm)]	SC554-100
Stainless Steel Cover Screws [M4-0.7 X 25mm] (Pkg 50)	SC583-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554XGASKET

