




TOP VIEW




SECTION B-B
SIDE VIEW




INSIDE BOX




SECTION A-A
END VIEW



STEEL PANEL
ORDER SEPARATELY



INSIDE LID



POLYCARBONATE
VERSION ONLY



FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 6 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 8-9 lbf-in (90-100 cN-m)

1554YA

1554YA Regular Enclosure

General Purpose ABS RAL-7035	1554YAGY
Polycarbonate RAL-7035	1554YA2GY
1554YA Clear / Smoke Lid Enclosure	
Polycarbonate Box / Clear Polycarbonate Lid	1554YA2GYCL
Polycarbonate Box / Smoke Polycarbonate Lid	1554YA2GYSL

ACCESSORIES

Steel Inner Panels	1554YPL
Steel Panel / P.C. Board Screw [M3-0.5 x 8mm Plated] (Pkg 100)	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#8 X 5/16" (6.4mm)]	SC554-100
Stainless Steel Cover Screws [M4-0.7 X 25mm] (Pkg 50)	SC583-50
Silicone Pre-formed Gasket Black (Pkg 2)	1554YGASKET



Dimensions:
mm
[inches]

www.hammondmfg.com