




TOP VIEW


SECTION B-B
SIDE VIEW




SECTION A-A
SIDE VIEW



INSIDE BOX



INSIDE LID



POLYCARBONATE
VERSION ONLY
cUL US LISTED
FILE #E65324
TYPE 4,4X6,6P

Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, styled lid, 4 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - V0A @ 3mm)
Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)

| 1555JL | | |
|---|-------------|--|
| Regular Enclosure | | |
| General Purpose ABS RAL-7035 | 1555JLGY | |
| Polycarbonate RAL-7035 | 1555JLGY | |
| ACCESSORIES | | |
| Steel Inner Panels | 1554JPL | |
| Steel Panel / P.C. Board Screw | 1591MM100 | |
| Steel Panel / P.C. Board Self Tapping Screw | 1598ATS100 | |
| Stainless Steel Cover Screws | SC576-50 | |
| Silicone Pre-formed Gasket Black (Pkg 2) | 1554JGASKET | |



HAMMOND
MANUFACTURING®

1555JL2GY

www.hammondmfg.com

Dimensions:
mm
[inches]