




**ENCLOSURE ASSEMBLY TOP VIEW**




**SECTION B-B  
SIDE VIEW**




**INSIDE BOX VIEW**



**SECTION A-A  
END VIEW**



**INSIDE LID VIEW**



POLYCARBONATE  
VERSION ONLY  
**UL** US LISTED  
FILE #E65324  
NEMA 4, 4X

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)  
Contact Factory (modshop@hammondmfg.com) for quotes  
Solid models of this enclosure available in .stp or .x\_t  
(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)

**NOTE**


Purchased assembly includes styled box, flanged lid, 4 cover screws, and preformed silicone gasket.  
General Purpose ABS version is not UL approved. (Matl UL94 - HB)  
Polycarbonate version is UL 508 approved. (Matl UL94 - 5VA @ 3mm)

**Recommended Cover screw torque -- 2.5 lbf-in (30 cN-m)**

**1555NF**

**1555NF Regular Enclosure**

General Purpose ABS RAL-7035	1555NF17GY
Polycarbonate RAL-7035	1555N2F17GY
<b>ACCESSORIES</b>	
Steel Inner Panels	1555NFPL
Silicone Pre-formed Gasket Black	1554NGASKET
Steel Panel / P.C. Board Self Tapping Screw [#4 X 1/4" (6.4mm) Plated]	1555TS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50



[www.hammondmfg.com](http://www.hammondmfg.com)

Dimensions:  
mm  
[inches]