




**TOP VIEW**



**SECTION B-B  
SIDE VIEW**




POLYCARBONATE  
VERSION ONLY  
c  US LISTED  
FILE #E65324  
TYPE 4,4X,6,6P



Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)  
Contact Factory ([modshop@hammfg.com](mailto:modshop@hammfg.com)) for quotes  
Solid models of this enclosure available in .stp or .x\_t  
(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)

| NOTE  |  |
|---|--|
| 4 cover screws, and<br>preformed silicone gasket.<br>General Purpose ABS version is not UL approved. (Matl UL94 - HB)<br>Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm) |  |
| <b>Recommended Cover screw torque -- 43-57 ozf-in (30-40 cN-m)</b>  |  |


| 1555N   |             |
|---|-------------|
| 1555N Regular Enclosure   |             |
| General Purpose ABS RAL-7035  | 1555NGY     |
| Polycarbonate RAL-7035  | 1555N2GY    |
| ACCESSORIES   |             |
| Steel Inner Panels  | 1554NPL     |
| Steel Panel / P.C. Board Screw<br>[M3-0.5 x 8mm Plated] (Pkg 100)                   | 1591MM100   |
| Steel Panel / P.C. Board Self Tapping Screw<br>[#6 X 1/4" (6.4mm) Plated] (Pkg 100) | 1598ATS100  |
| Stainless Steel Cover Screws<br>[M4-0.7 X 20mm] (Pkg 50)                            | SC576-50    |
| Silicone Pre-formed Gasket Black (Pkg 2)  | 1554NGASKET |



**SECTION A-A  
SIDE VIEW**



**INSIDE BOX**



**INSIDE LID**

Dimensions:  
mm  
[inches]