



POLYCARBONATE
VERSION ONLY
cUL US LISTED
FILE #E65324
TYPE 4.4X.6.6P



Dimensions:
mm
[inches]



NOTE
Purchased assembly includes box, styled lid, 6 cover screws, and preformed silicone gasket.
General Purpose ABS version is not UL approved. (Mail UL94 - HB)
Polycarbonate version is UL 508A approved. (Mail UL94 - 5VA @ 3mm)
Recommended Cover screw torque --43-57 oz/in (30-40 cN-m)

1555VAL			
1555VAL Regular Enclosure			
General Purpose ABS RAL-7035		1555VALGY	
Polycarbonate RAL-7035		1555VAL2GY	
ACCESSORIES			
Steel Inner Panels		1554VALPL	
Steel Fanel / P.C. Board Screw (M3.0 5.1 8mm Plated) (Pkg 100)		1591MVM100	
Steel Panel / P.C. Board Self Tapping Screw (#6 X 1/4" (6.4mm) Plated) (Pkg 100)		1598ATS100	
Stainless Steel Cover Screws (M4.0 7 X 25mm) (Pkg 50)		SC583-50	
Silicone Preformed Gasket Black (Pkg 2)		1554VAGASKET	

