



**Dimensions:**  
mm  
[inches]

POLYCARBONATE  
[ VERSION ONLY ]



FILE #E65324  
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)  
Contact Factory (modshop@hammfg.com) for quotes  
Solid models of this enclosure available in .stp or .x\_t.  
(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)

**NOTE**

Purchased assembly includes box, lid, 4 cover screws, preformed silicone gasket, 4 rubber feet, 4 wall mount foot screws, and 4 wall mount feet.  
General Purpose ABS version is not UL approved. (Matl UL94 - HB)  
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

**Recommended Cover Screw Torque - 71-85 ozf-in ( 50-60 cN-m)**

<b>1557</b>		
<b>1557DA Enclosure</b>		
	General Purpose ABS Black Enclosure	1557DABK
	General Purpose ABS Grey Enclosure	1557DAGY
	Polycarbonate Black Enclosure	1557DA2BK
	Polycarbonate Grey Enclosure	1557DA2GY
<b>ACCESSORIES</b>		
	Silicone Pre-formed Gasket Black (Pkg 2)	1557DGASKET
	Clear Rubber Feet (Pkg 24)	1421T6CL
	Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
	Steel P.C.Board Screw [#6 X 1/4" Self Tapping] (Pkg 50)	SC526-50
	Stainless Steel Wall Mount foot Screw [#8 X 3/8" Self Tapping] (Pkg 50)	SC556-50
Wall Mout Foot Kit [wall mount foot ] (Pkg 24) [#8 X 3/8" Self Tapping] (Pkg 24)	General Purpose ABS Grey	1557FOOTGY-24
	General Purpose ABS Black	1557FOOTBK-24
	POLYCARBONATE Grey	1557FOOT2GY-24
	POLYCARBONATE Black	1557FOOT2BK-24

