



POLYCARBONATE  
VERSION ONLY



FILE #E65324  
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)

Contact Factory (modshop@hammfg.com) for quotes

Solid models of this enclosure available in .stp or .x\_t.

(Part number and text placement/orientation on our products are subject to change,  
we do not recommend using them as a locating reference for modification purposes)

**NOTE**

Purchased assembly includes box, lid, 4 cover screws, preformed silicone gasket, 4 rubber feet, 4 wall mount foot screws, and 4 wall mount feet.

General Purpose ABS version is not UL approved. (Matl UL94 - HB)

Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

**Recommended Cover Screw Torque - 71-85 ozf-in ( 50-60 cN-m)**

1557									
1557F Enclosure									
General Purpose ABS Black Enclosure		1557FBK							
General Purpose ABS Grey Enclosure		1557FGY							
Polycarbonate Black Enclosure		1557F2BK							
Polycarbonate Grey Enclosure		1557F2GY							
ACCESSORIES									
Silicone Pre-formed Gasket Black (Pkg 2)		1557FGASKET							
Clear Rubber Feet (Pkg 24)		1421T6CL							
5	Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50							
	Steel P.C.Board Screw [#6 X 1/4" Self Tapping] (Pkg 50)	SC526-50							
	Stainless Steel Wall Mount foot Screw [#8 X 3/8" Self Tapping] (Pkg 50)	SC556-50							
	Wall Mout Foot Kit [wall mount foot ] (Pkg 24) [#8 X 3/8" Self Tapping] (Pkg 24)	<table><tr><td>General Purpose ABS Grey</td><td>1557FOOTGY-24</td></tr><tr><td>General Purpose ABS Black</td><td>1557FOOTBK-24</td></tr><tr><td>POLYCARBONATE Grey</td><td>1557FOOT2GY-24</td></tr><tr><td>POLYCARBONATE Black</td><td>1557FOOT2BK-24</td></tr></table>	General Purpose ABS Grey	1557FOOTGY-24	General Purpose ABS Black	1557FOOTBK-24	POLYCARBONATE Grey	1557FOOT2GY-24	POLYCARBONATE Black
General Purpose ABS Grey	1557FOOTGY-24								
General Purpose ABS Black	1557FOOTBK-24								
POLYCARBONATE Grey	1557FOOT2GY-24								
POLYCARBONATE Black	1557FOOT2BK-24								



**Dimensions:**  
mm  
[inches]