




TOP VIEW




SECTION B-B
SIDE VIEW




INSIDE LID




SECTION A-A
END VIEW




WALL MOUNT FOOT VIEW



WALL MOUNT
FOOT



INSIDE BOX



POLYCARBONATE
VERSION ONLY

UL US LISTED
FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t.
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes box, lid, 4 cover screws, preformed silicone gasket, 4 rubber feet, 4 wall mount foot screws, and 4 wall mount feet.
General Purpose ABS version is not UL approved. (Matl UL94 - HB)
Polycarbonate version is UL 508A approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover Screw Torque - 71-85 ozf-in (50-60 cN-m)

1557

1557HA Enclosure

General Purpose ABS Black Enclosure	1557HABK
General Purpose ABS Grey Enclosure	1557HAGY
Polycarbonate Black Enclosure	1557HA2BK
Polycarbonate Grey Enclosure	1557HA2GY

ACCESSORIES

Silicone Pre-formed Gasket Black (Pkg 2)	1557HGASKET
Clear Rubber Feet (Pkg 24)	1421T6CL
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50
Steel P.C.Board Screw [#6 X 1/4" Self Tapping] (Pkg 50)	SC526-50
Stainless Steel Wall Mount foot Screw [#8 X 3/8" Self Tapping] (Pkg 50)	SC556-50

Wall Mout Foot Kit [wall mount foot] (Pkg 24) [#8 X 3/8" Self Tapping] (Pkg 24)	General Purpose ABS Grey	1557FOOTGY-24
	General Purpose ABS Black	1557FOOTBK-24
	POLYCARBONATE Grey	1557FOOT2GY-24
	POLYCARBONATE Black	1557FOOT2BK-24

**HAMMOND
MANUFACTURING®**

1557HA

www.hammondmfg.com

Dimensions:
mm
[inches]