





SECTION A-A



SECTION B-B




FOR REFERENCE ONLY
MOUNTING FEET SHOWN AS INSTALLED



THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2020 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS
ASSEMBLY:
1. (1) POLYCARBONATE ACCESSORY KIT (WPPCACCKIT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE.
2. (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

NEMA 250: TYPE 1, 3R, 4, 4X, 12 IEC 60529: IP66			STANDARD P/N: AH1084SS		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX + 0.03 - 0.010		
COLOR: N/A COLOR STANDARD: PANTONE 7541 C			CUSTOMER DWG:		<div><div></div><div>AttoBox</div><div>A BROBBY ENCLOSURES™ BRAND</div></div> <div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378</div>						
MATERIAL: POLYCARBONATE											
REVISION HISTORY											
REV	DESCRIPTION	DATE	ENG	DRAWN BY	DATE	CUSTOMER			DWG		
-	-	-	-	AA	8/15/20				AH1084SS		
-	-	-	-	SCALE		DESCRIPTION			PART NUMBER		
-	-	-	-	DO NOT SCALE		STANDARD ENCLOSURE			ATAH1084SS		



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378