







FOR REFERENCE ONLY  
MOUNTING FEET SHOWN AS INSTALLED



SECTION A-A



SECTION B-B



THIS DRAWING IS THE SOLE AND EXCLUSIVE  
PROPERTY OF ROBROY ENCLOSURES.  
NO PART OF THIS DRAWING MAY BE  
REPRODUCED, DISTRIBUTED, OR PUBLICALLY  
DISPLAYED IN ANY FORM OR BY ANY MEANS  
WITHOUT THE EXPRESS WRITTEN  
PERMISSION OF ROBROY ENCLOSURES.  
ALL RIGHTS RESERVED  
UNDER THE COPYRIGHT LAWS.  
COPYRIGHT © 2020 ROBROY ENCLOSURES

### SPECIAL REQUIREMENTS

**SPECIAL REQUIREMENTS**

**ASSEMBLY:**

1. (1) ACCESSORY KIT (WPPCACCKIT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE

2. (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

NEMA 250: TYPE	1, 3R, 4, 4X, 12
IEC 60529:	IP66

COLOR: N/A  
COLOR STANDARD: PANTONE 7541 C

STANDARD P/N:	AH14126SS
---------------	-----------

	CUSTOMER DWG:
--	---------------

	ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED
--	--

--	--

# Altobello

# ALLIB

## ROBROY ENCLOSURES

E	CUSTOMER
---	----------

20

DESCRIPTION
-------------

E	STANDARD ENCL
---	---------------

TOLERANCES	.XX	.XXX
UNLESS SPECIFIED	± 0.03	± 0.010

Robroy Enclosure

500 Maple Street

**Belding, Michigan 48824**  
Phone: 616-794-0700

BRAND Phone: 616-749-07  
Fax: 616-749-33

	DWG
--	-----

AH14126S

	PART NUMBER
--	-------------

SURE	ATAH14126SS
------	-------------

[illegible]

 <b>A ROBROY ENCLOSURES™ BRAND</b>		Belding, Michigan 48801 Phone: 616-794-0701 Fax: 616-749-3133	
DRAWN BY	DATE	CUSTOMER	DWG
AA	8/15/20		AH14126S
SCALE	DESCRIPTION	PART NUMBER	
DO NOT SCALE	STANDARD ENCLOSURE	ATAH14126SS	