


THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2020 ROBROY ENCLOSURES.

- ASSEMBLY:**
- 1. (1) ACCESSORY KIT (WPPCACCKIT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
 - 2. (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3R, 4, 4X, 12 IEC 60529: IP66			STANDARD P/N: AH864CSS		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010		
COLOR: N/A COLOR STANDARD: PANTONE 7541 C			CUSTOMER DWG:										
MATERIAL: POLYCARBONATE							Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378						
REVISION HISTORY													
REV	DESCRIPTION		DATE	ENG	DRAWN BY	DATE	CUSTOMER		DWG				
-	-		-	-	AA	8/15/20			AH864CSS				
-	-		-	-	SCALE		DESCRIPTION		PART NUMBER				
-	-		-	-	DO NOT SCALE		STANDARD ENCLOSURE		ATAH864CSS				
-	-		-	-									



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378