


THIS DRAWING IS THE SOLE AND EXCLUSIVE  
PROPERTY OF ROBROY ENCLOSURES.  
NO PART OF THIS DRAWING MAY BE  
REPRODUCED, DISTRIBUTED, OR PUBLICALLY  
DISPLAYED IN ANY FORM OR BY ANY MEANS  
WITHOUT THE EXPRESS WRITTEN  
PERMISSION OF ROBROY ENCLOSURES.  
ALL RIGHTS RESERVED  
UNDER THE COPYRIGHT LAWS.  
COPYRIGHT © 2020 ROBROY ENCLOSURES

<b>ASSEMBLY:</b> 1. (1) ACCESSORY KIT (WPPCACCKIT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE 2. (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON		<b>SPECIAL REQUIREMENTS</b> NEMA 250: TYPE 1, 3R, 4, 4X, 12 IEC 60529: IP66 COLOR: N/A COLOR STANDARD: PANTONE 7541 C		STANDARD P/N: AH864SS CUSTOMER DWG:		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED .XX ± 0.03 .XXX ± 0.010							
		MATERIAL: POLYCARBONATE		 <b>AttaBox</b> A ROBROY ENCLOSURES™ BRAND		<b>Robroy Enclosures</b> 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3376									
		REVISION HISTORY													
REV		DESCRIPTION		DATE		ENG		DRAWN BY		DATE		CUSTOMER		DWG	
-		-		-		-		AA		8/15/20				AH864SS	
-		-		-		-		SCALE		DO NOT SCALE		DESCRIPTION		PART NUMBER	
-		-		-		-						STANDARD ENCLOSURE		ATAH864SS	
-		-		-		-									
-		-		-		-									