






ATM1500 Cutout
Units: inch [mm] Full scale
 AUTOMATIONDIRECT .com



2.65
[67]





2.4
[61]




ATM1500

Units: inch [mm]
Full scale

 **AUTOMATIONDIRECT**.com



ATM1500T Cutout
Units: inch [mm] Full scale
 AUTOMATIONDIRECT .com



12.8
[325]

15.8
[401]


2.65
[67]


2.4
[61]




ATM1500T

Units: inch [mm]
Full scale


 **AUTOMATIONDIRECT**.com



ATM1700 Cutout
Units: inch [mm] Full scale
 AUTOMATIONDIRECT .com



2.85
[72]





2.60
[66]




ATM1700

Units: inch [mm]
Full scale


 **AUTOMATIONDIRECT**.com



ATM1700T Cutout
Units: inch [mm] Full scale
 AUTOMATIONDIRECT .com




2.85
[72]








2.60
[66]

ATM1700T

Units: inch [mm]
Full scale



ATM1900 Cutout
Units: inch [mm] Full scale
 AUTOMATIONDIRECT .com




ATM1900


Units: inch [mm]
Full scale



 **AUTOMATIONDIRECT**.com

14.90±0.02
[378±0.5]




17.75±0.02
[451±0.5]


ATM1900T Cutout
Units: inch [mm] Full scale
 AUTOMATIONDIRECT .com



18.66
[474]



2.95
[75]



2.70
[69]

ATM1900T

Units: inch [mm]
Full scale

 **AUTOMATIONDIRECT**.com