



THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2017 ROBROY ENCLOSURES

END USER NOTES:
1. TORQUE COVER SCREWS TO 9-17 IN.-LBS. TO MAINTAIN RATINGS

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3R, 4, 4X, 12 IEC 60529: IP66 COLOR: LIGHT GREY COLOR STANDARD: RAL 7035				STANDARD P/N: BB251690W		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	.XXX ± 0.010
MATERIAL: POLYCARBONATE				<div>AttaBox™</div> <div>Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-704-0700 Fax: 616-749-3378</div>							
REVISION HISTORY											
REV	DESCRIPTION	DATE	ENG	DRAWN BY		DATE	CUSTOMER		DWG		
-	-	-	-	E91		04/17/17			BB251690W		
-	-	-	-								
-	-	-	-								
-	-	-	-								
-	-	-	-								
-	-	-	-								
-	-	-	-								
				SCALE		DESCRIPTION		PART NUMBER			
				DO NOT SCALE		STANDARD ENCLOSURE		ATBB251690W			