



END USER NOTES:
1. TORQUE COVER SCREWS TO 9-17 IN.-LBS. TO MAINTAIN RATINGS

THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2017 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3R, 4, 4X, 12 IEC 60529: IP66 COLOR: LIGHT GREY COLOR STANDARD: RAL 7035				STANDARD P/N: BBCC161214W		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	XXX ± 0.010		
MATERIAL: POLYCARBONATE						<div>AttaBox™</div>						Roboc Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378	
REVISION HISTORY												DWG BBCC161214W	
REV	DESCRIPTION				DATE	ENG	WWW.ATTABOX.COM DRAWN BY DATE E91 04/14/17		CUSTOMER		PART NUMBER ATBBCC161214W		
-	-				-	-	SCALE		DESCRIPTION		PART NUMBER		
-	-				-	-	DO NOT SCALE		STANDARD ENCLOSURE		ATBBCC161214W		
-	-				-	-							
-	-				-	-							
-	-				-	-							
-	-				-	-							
-	-				-	-							