


#### Color and Length Part Number Combinations

##### C5E-STPnn-Sxx

nn	Color	Sxx	Length
BK	Black	S3	3FT
BL	Blue	S7	7FT
GN	Green	S10	10FT
GY	Grey	S14	14FT
OR	Orange	S25	25FT
PL	Purple	S50	50FT
YL	Yellow		
RD	Red		

#### Notes:

1. CABLE - UL Type CM, 24AWG\*4P + AEB, OD: 6.0MM, Rated 75°C
2. RJ45 8P8C Shielded Plug
3. Minimum Bending Radius: 48MM [1.88"]
4. Operating Temperature: 0-60°C [32-140°F]

C5E-STPnn-Sxx	
Rev: original	Date: 12/10/2014
Units: mm [inches]	
Scale: none	
Ethernet Patch Cable	
 <b>AUTOMATIONDIRECT</b> .com	