


Color and Length Part Number Combinations

C5E-STPnn-Cxx

nn	Color	Cxx	Length
OR	Orange	C3	3FT
YL	Yellow	C7	7FT
		C10	10FT
		C14	14FT
		C25	25FT
		C50	50FT

Notes:

1. CABLE - UL Type CM, 24AWG*4P + AEB, OD: 6.0MM, Rated 75°C
2. RJ45 8P8C Shielded Plug
3. Minimum Bending Radius: 48MM [1.88"]
4. Operating Temperature: 0-60°C [32-140°F]

C5E-STPnn-Cxx	
Rev: original	Date: 12/10/2014
Units: mm [inches]	
Scale: none	
Ethernet Crossover Cable	
 AUTOMATIONDIRECT .com	