





1/2-13 ∇ 0.75 [19.1]
THREAD X4



3/8-24
X4
BOTH ENDS



NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

D252030DT-MC
Units: inches [mm] Scale: Full
NITRA NFPA CYLINDER: 3.25" BORE, 3" STROKE, MAG PISTON, CUSHIONED

