

General tolerances if not otherwise specified				
NDM DIM mm		Tool Class		
From	To	A	B	C
(1)	6	± 0.05	± 0.1	± 0.2
(6)	30	± 0.1	± 0.2	± 0.5
(30)	100	± 0.15	± 0.3	± 0.8
(100)	300	± 0.2	± 0.5	± 1.2
(300)	1000	± 0.3	± 0.8	± 2
Holes H 13				

