


END USER NOTES:
1. TORQUE COVER SCREWS TO 17-22 IN.-LBS. TO MAINTAIN RATINGS

THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2017 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3, 3S, 4X, 6, 6P, 12 IEC 60529: IP66, IP67, IP68 COLOR: GLACIER GRAY COLOR STANDARD: PANTONE 428 C			STANDARD P/N: DU16165W CUSTOMER DWG:		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010	
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)								Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378				
REVISION HISTORY												
REV	DESCRIPTION			DATE	ENG							
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-							
-	-			-	-							
					DRAWN BY: DATE		CUSTOMER			DWG		
					E91 05/02/17					DU16165W		
					SCALE		DESCRIPTION			PART NUMBER		
					DO NOT SCALE		STANDARD ENCLOSURE			ATDU16165W		