


10.1
[0.40]

10.8
[0.43]

5.0
[0.20]

8.6
[0.34]




Ø 4.5
[0.18]
THRU

11.7
[0.46]


26.0
[1.02]

30.0
[1.18]


15.0
[0.59]



5.4
[0.21]



VIEW SHOWS LEVER TRAVEL
IN ALL POSITIONS



Ø 4.0
[0.16]
OUTLET (2)

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

EVP-CA-T

Units: mm [inches]

Scale: Full

MNL VLV, 3/2 NC, 1-WAY ROLLER

AUTOMATIONDIRECT.com