

FBJ100




Units: mm [inch]


Scale: Full




() denotes # of similar objects


\emptyset denotes diameter








| |
|--|
| FBJ200 |
| Units: mm [inch] |
| Scale: Full |
| () denotes # of similar objects |
| Ø denotes diameter |
|  AUTOMATIONDIRECT .com |





| |
|--|
| FBJ200T |
| Units: mm [inch] |
| Scale: Full |
| < > denotes # of similar objects |
| ∅ denotes diameter |
|  AUTOMATIONDIRECT .com |



FBJ30

Units: mm [inch]
Scale: Full
() denotes # of similar objects
 ϕ denotes diameter
Amp Rating: 30A

 **AUTOMATIONDIRECT**.com



FB30CDT

Units: mm [Inch]




Scale: Full

() denotes # of similar objects

∅ denotes diameter

— line indicates moving part

AUTOMATIONDIRECT.com



FBJ30T

Units: mm [inch]




Scale: Full

() denotes # of similar objects

ø denotes diameter


Amp Rating: 30A




 **AUTOMATIONDIRECT**.com



FBJ60


Units: mm [inch]
Scale: Full
() denotes # of similar objects
Ø denotes diameter
Amp Rating: 60A

 **AUTOMATIONDIRECT**.com





FBJ60T


Units: mm [inch]
Scale: Full
() denotes # of similar objects
Ø denotes diameter
Amp Rating: 60A

 **AUTOMATIONDIRECT**.com


DOOR DRILLING



USE WITH
MOUNTING NUT






USE WITH
2 MOUNTING
SCREWS




HDPB

Units: mm [inch]
Scale: Full
< > denotes # of similar objects
Ø denotes diameter

 **AUTOMATIONDIRECT**.com



DOOR DRILLING





HGPB

Units: mm [inch]


Scale: Full

() denotes # of similar objects

∅ denotes diameter



DOOR DRILLING



HGPBL




Units: mm [inch]


Scale: Full




() denotes # of similar objects


ϕ denotes diameter












| |
|--|
| SC1000 |
| Units: mm [inch] |
| Scale: Full |
| () denotes # of similar objects |
| Ø denotes diameter |
| Amp Rating: 1000A |
|  AUTOMATIONDIRECT .com |



| |
|--|
| SC400 |
| Units: mm [inch] |
| Scale: Full |
| () denotes # of similar objects |
| Ø denotes diameter |
| Amp Rating: 400A |
|  AUTOMATIONDIRECT .com |



| SC600 |
|--|
| Units: mm [inch] |
| Scale: Full |
| () denotes # of similar objects |
| Ø denotes diameter |
| Amp Rating: 600A |
|  AUTOMATIONDIRECT .com |



SCV100

Units: mm [inch]




Scale: Full


() denotes # of similar objects


ϕ denotes diameter

Amp Rating: 100A









| SCV200 |
|--|
| Units: mm [inch] |
| Scale: Full |
| () denotes # of similar objects |
| ∅ denotes diameter |
| Amp Rating: 200A |
|  AUTOMATIONDIRECT .com |



SCV30

Units: mm [inch]
Scale: Full
() denotes # of similar objects
 \varnothing denotes diameter
Amp Rating: 30A

 **AUTOMATIONDIRECT**.com



SCV60

Units: mm [inch]

Scale: Full

() denotes # of similar objects

ø denotes diameter

Amp Rating: 60A

 **AUTOMATIONDIRECT**.com