




8 7 6 5 4 3 2 1




ASSEMBLY - VIEW FROM FRONT




ASSEMBLY - VIEW FROM SIDE



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM BOTTOM



ASSEMBLY - VIEW FROM BACK

FLHTF800A115

Housing - Aluminum Alloy

Rating - 120 VAC, 60 Hz, 800 W

Approvals - UL Recognized Standard UL 508A
- CSA Standard C22.2 No. 88



HAMMOND
MANUFACTURING™



FLHTF800A115

www.hammondmfg.com

8 7 6 5 4 3 2 1