



ProSense FLOAT LIQUID LEVEL SWITCH, HORIZONTAL SIDE MOUNT, 3.31in INSERTION LENGTH, 0.65in DIAMETER FLOAT, POLYPROPYLENE WETTED PARTS, -40 to 221 DEG F, DUAL 5/8-11 MALE UNC WITH GASKET, WASHER AND NUT PROCESS CONNECTION, SPST REED SWITCH, N.O./N.C. SELECTABLE

FLS-HS-300_RevB

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
10/4/2023

SHEET 1 OF 1