



FOR REFERENCE ONLY  
MOUNTING FEET SHOWN AS INSTALLED

SPECIAL REQUIREMENTS				NEMA 250: TYPE 1, 3, 3S, 4X, 12, 13 IEC 60529: IP66		STANDARD P/N: FR121006HPL		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03 XXX ± 0.010	
<b>ASSEMBLY:</b> 1. MOUNTING FEET SHOWN AS INSTALLED - FOR REFERENCE ONLY - SOLD SEPARATELY - FREEDOM SERIES MOUNTING FOOT KIT (FEFRMGFTKIT) - INCLUDES (4) #10-32 x 7/16 FLAT HEAD PHILLIPS HEAD SCREWS (RMSC10-32X7/16FHPH) 2. (1) FREEDOM SERIES SCREW PACK (WP4PKBP) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE <b>HARDWARE INCLUDED:</b> - (4) #10-32 x 3/8 PAN HEAD SCREW (RMSC10/32X3/8ZN) - (4) #10 WASHER (RMMWAS10ZN)				COLOR: GLACIER GREY (WPR3X13) COLOR STANDARD: PANTONE 428 C		CUSTOMER DWG:							
				MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)									
REV	DESCRIPTION	DATE	ENG	REVISION HISTORY									
-	-	-	-										
-	-	-	-										
-	-	-	-										
-	-	-	-										
-	-	-	-										
-	-	-	-										
-	-	-	-										