









FOR REFERENCE ONLY
MOUNTING FEET SHOWN AS INSTALLED



DETAIL C
(4X)



THIS DRAWING IS THE SOLE AND EXCLUSIVE
PROPERTY OF ROBROY ENCLOSURES.
NO PART OF THIS DRAWING MAY BE
REPRODUCED, DISTRIBUTED, OR PUBLICALLY
DISPLAYED IN ANY FORM OR BY ANY MEANS
WITHOUT THE EXPRESS WRITTEN
PERMISSION OF ROBROY ENCLOSURES.
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS.
COPYRIGHT © 2017 ROBROY ENCLOSURES


END USER NOTES:
1. TORQUE COVER SCREWS TO 20-24 IN.-LBS. TO MAINTAIN RATINGS

SPECIAL REQUIREMENTS

1. MOUNTING FEET SHOWN AS INSTALLED - FOR REFERENCE ONLY
-SOLD SEPARATELY
-FREEDOM SYSTEM MOUNTING FOOT KIT (FFRMFGT)KIT
-INCLUDES 4) #10-32 x 1/16 FLAT HEAD PHILLIPS HEAD SCREWS (RMS10-32X7/16PH)14

2. 1) FREEDOM SYSTEM SCREW PAK (WP2PKFRB) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
HARDWARE INCLUDED:

- (2) #10-32 x 1-1/4 PAN HEAD COMBINATION DRIVE SCREW (RMS10-32X1-1/4COM)
- 4) #10-32 x 1/4 PAN HEAD SCREW (RMS10-32X3/8PN)
- (2) WASHER (RMSW10ZN)
- (2) O-RING FOR COVER SCREW (RMSAS668007)

NEMA 250: TYPE 1, 3, 3S, 4X, 12, 13 IEC 60529: IP66 COLOR: GLACIER GREY (WPR3X13) COLOR STANDARD: PANTONE 428 C		STANDARD P/N: FR161408HW CUSTOMER DWG:		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	.XXX ± 0.010
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)						Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378			
REVISION HISTORY									
REV	DESCRIPTION	DATE	ENG	WWW.ATTABOX.COM DRAWN BY DATE E91 05/09/17		CUSTOMER		DWG FR161408HW	
-	-	-	-	SCALE DO NOT SCALE		DESCRIPTION STANDARD ENCLOSURE		PART NUMBER ATRFR161408HW	
-	-	-	-						
-	-	-	-						
-	-	-	-						