



FOR REFERENCE ONLY
MOUNTING FEET SHOWN AS INSTALLED

SECTION B-B

DETAIL C
(4X)

END USER NOTES:
1. TORQUE COVER SCREWS TO 20-24 IN.-LBS. TO MAINTAIN RATINGS

THIS DRAWING IS THE SOLE AND EXCLUSIVE
PROPERTY OF ROBROY ENCLOSURES.
NO PART OF THIS DRAWING MAY BE
REPRODUCED, DISTRIBUTED, OR PUBLICALLY
DISPLAYED IN ANY FORM OR BY ANY MEANS
WITHOUT THE EXPRESS WRITTEN
PERMISSION OF ROBROY ENCLOSURES.
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS.
COPYRIGHT © 2017 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

- ASSEMBLY:
1. MOUNTING FEET SHOWN AS INSTALLED - FOR REFERENCE ONLY
- SOLD SEPARATELY
- FREEDOM SERIES MOUNTING FOOT KIT (FEFRMGFTKIT)
- INCLUDES (4) #10-32 x 7/16 FLAT HEAD PHILLIPS HEAD SCREWS (RMSC10-32X7/16FPH)
2. (1) FREEDOM SERIES SCREW PACK (WP2PKFRBP) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
HARDWARE INCLUDED:
- (2) #10-32 x 1-1/4 PAN HEAD COMBINATION DRIVE SCREW (RMSC10-32X1-1/4COM)
- (4) #10-32 x 3/8 PAN HEAD SCREW (RMSC10-32X3/8ZN)
- (4) #10 WASHER (RMWAS10ZN)
- (2) O-RING FOR COVER SCREW(RMAS568007)

NEMA 250: TYPE 1, 3, 3S, 4X, 12, 13 IEC 60529: IP66			STANDARD P/N: FR80604HW		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010	
COLOR: GLACIER GREY (WPR3X13) COLOR STANDARD: PANTONE 428 C			CUSTOMER DWG:									
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)					<div>AttaBox</div>							
REVISION HISTORY												
REV	DESCRIPTION		DATE	ENG								
-			-	-								
-			-	-								
-			-	-								
-			-	-								
-			-	-								
-			-	-								
-			-	-								
-			-	-								
					SCALE		DESCRIPTION		PART NUMBER			
					DO NOT SCALE		STANDARD ENCLOSURE		ATFR80604HW			