

NOTES :

1. WIRE : UL2464 COMPUTER CABLE, AL-MYLAR FOIL & BRAID SHIELD TYPE, 28AWG, NO. OF CORE : 8, THE COLOR OF CABLE : BLACK, RATED TEMPERATURE : 80°C, RATED VOLTAGE : 300 VOLTS.
2. CIRCUIT : 3-11, 5-9, 7-7, 11-3, 4-12, 6-10, 8-8, 10-6, 12-4.
GROUND CONNECTION : ① (DRAIN WIRE) - ③ (DRAIN WIRE).
3. A : HOUSING: UL94V-1, PBT, BLACK.
CURRENT RATING: 3A, VOLTAGE RATING: 250V.
VENDOR P/N: 254I-K-14PD OR EQUIVALENT.
TERMINAL: VENDOR P/N: 254I-T-G OR EQUIVALENT.
VENDOR: JAWS OR EQUIVALENT.
4. B : FIGURE "1" (SR MODELING).
5. ASSEMBLY : FIGURE "2", FIGURE "3".
6. PACKAGE : FIGURE "4".

FIGURE "2" (ASSEMBLY DRAWING).




FIGURE "3" (ASSEMBLY).




FIGURE "1"
(SR MODELING DIMENSION)





FIGURE "4" (PACKAGE)



PART#	t(mm)	L(mm)	L(in)
GS-CBL2-1L	15	1000	39.4
GS-CBL2-3L	20	3000	118.1
GS-CBL2-5L	30	5000	196.8

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

GS-CBL2-5L

Units: mm [inches]

Scale: Full

**DURApulse KEYPAD MOUNTING
CABLE, 5m LENGTH**

AUTOMATIONDIRECT