





LINE SIDE



LOAD SIDE

Metric +/- 0.13mm
Inches +/- 0.005"
Angular +/- 2°

HPB10S-3
Units: mm [inch]
Full Scale
DISTRIBUTION BLOCK
OPEN TYPE, UL LISTED
175A, 3 POLE, 1-IN, STUD
 AUTOMATIONDIRECT .com