



SPECIAL REQUIREMENTS

NEMA 250 TYPE 1, 3R, 4X, 6P, 12			STANDARD PIN:		ALL DIMENSIONS ARE IN INCHES		TOLERANCES	
E.G. 6020, 6040, 6060			CUSTOMER DWG:		UNLESS OTHERWISE SPECIFIED		UNLESS SPECIFIED	
COLOR: GLACIER GRAY (RFP3013)							XX .003	
COLOR STANDARD: PANTONE 428 C							XXX .010	
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)								
REVISION HISTORY								
REV	DESCRIPTION			DATE	ENG			
-	-			-	-			
-	-			-	-			
-	-			-	-			
DRAWN BY				DATE		CUSTOMER		DWG
E81				06/22/16				HW-J161406CHTL
SCALE				DESCRIPTION				PART NUMBER
DO NOT SCALE				ENCL JIC 4X 16X14X6 FG HLL				HW-J161406CHTL