



SPECIAL REQUIREMENTS

NEMA 250 TYPE 1, 3, 3R, 4, 4X, 12, 13 REQ 60200				STANDARD PIN: CUSTOMER DWG:		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		XX ± 0.03	XXX ± 0.010
COLOR: GLACIER GRAY (R6P3013) COLOR STANDARD: PANTONE 428 C				MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)		<div>HUBBELL- WIEGMANN</div>					
REVISION HISTORY											
REV	DESCRIPTION		DATE	ENG							
-	-		-	-							
DRAWN BY		DATE	CUSTOMER		DWG						
E81		08/15/2016			HW-J2020103PT						
SCALE		DESCRIPTION		PART NUMBER							
DO NOT SCALE		ENCL JIC 20X20X10 FG 3 POINT LATCH		HW-J2020103PT							