


ECCENTRICITY OF THREADED PORTION OF SHAFT IS HELD WITHING 0.004 GAGE READING WITH THE INDICATOR ON O.D. OF GROUND RING GAGE AS SHOWN, THE GAGE BEING STATIONARY WITH RESPECT TO THE ROTOR.



NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

J064A	
Units: inches [mm]	
Scale: Full	
MARATHON AC INDUCTION MOTOR, GENERAL PURPOSE PUMP, 1.5 HP, 3-PH, 208-230/460 VAC, 3450 RPM, TEFC, 56J FRAME, ROLLED STEEL, RIGID BASE/C-FACE MOUNT	
<b>AUTOMATIONDIRECT</b> <sup>®</sup>	